

## Compression Deadend

By FARGO  
Catalog # [A031021NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Horizontal Eye, for ACSR 477 kcmil 26/7, Without Terminal



\*Representative Image

### Features

- For use with ACSR code name Hawk
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

### General

Compression Method	Uni-Grip (single die system)
Die Size	10CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Terminal Option	No
Type	Eye
UPC	096359366164

### Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.858 in
Length Before Compression	14.9 in
Messenger Diameter Range	0 - 0
Weight	2.210 lb
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Hawk-477-26/7
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)