

Compression Deadend

By FARGO
Catalog # [A031133](#)

Compression Deadend, Uni-Grip, Single Tongue, Horizontal Eye, for ACSR 636 kcmil 26/7, With Terminal



*Representative Image

Features

- For use with ACSR code name Grosbeak
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal & Mounting Hardware included

General

Compression Method	Uni-Grip (single die system)
Die Size	11CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Type	Eye
UPC	096359482802

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	0.99 in
Length Before Compression	16.3 in
Messenger Diameter Range	0 - 0
Weight	4.620 lb
Width - Pad	3 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Grosbeak-636-26/7
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)