

Compression Deadend

By FARGO
Catalog # [A041021NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Horizontal Eye, for ACSR 477 kcmil 26/7, Without Terminals



*Representative Image

Features

- For use with ACSR code name Hawk
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

| | |
|----------------------|---|
| Compression Method | Uni-Grip (single die system) |
| Die Size | 10CD |
| Material | Aluminum; Steel |
| Material - Body | Seamless Extruded Aluminum Alloy |
| Material - Eye | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Number of Bolt Holes | 2 |
| Press Minimum | 60 to |
| Product Category | Eye |
| Style | Uni-Grip, Double Tongue, Horizontal Eye |
| Terminal Option | No |
| Type | Eye |

Dimensions

| | |
|------------------------------|----------|
| Diameter - Clamping Hardware | 0 in |
| Diameter - Outside | 0.858 in |
| Length Before Compression | 14.9 in |
| Messenger Diameter Range | 0 - 0 |
| Width - Pad | 2 in |

Electrical Ratings

| | |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

| | |
|---------------------------------|--------------------|
| Clamping Range | 0- 0 |
| Conductor Compatibility | ACSR-Hawk-477-26/7 |
| Conductor Diameter (Main) Range | 0 - 0 |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)