

# Compression Deadend

By FARGO  
Catalog # [A041030](#)

Compression Deadend, Uni-Grip, Double Tongue, Horizontal Eye, for ACSR 636 kcmil 36/1, With Terminals



\*Representative Image

## Features

- For use with ACSR code name Swift
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal & Mounting Hardware included

## General

|                      |   |
|----------------------|---|
| Compression Method   | Uni-Grip (single die system)            |
| Die Size             | 10CD                                    |
| Material             | Aluminum; Steel                         |
| Material - Body      | Seamless Extruded Aluminum Alloy        |
| Material - Eye       | Galvanized Forged Steel                 |
| Material - Hardware  | Aluminum Alloy                          |
| Material - Terminal  | Seamless Extruded Aluminum Alloy        |
| Number of Bolt Holes | 2                                       |
| Press Minimum        | 60 to                                   |
| Product Category     | Eye                                     |
| Style                | Uni-Grip, Double Tongue, Horizontal Eye |
| Type                 | Eye                                     |

## Dimensions

|                              |          |
|------------------------------|----------|
| Diameter - Clamping Hardware | 0 in     |
| Diameter - Outside           | 0.927 in |
| Length Before Compression    | 14.9 in  |
| Messenger Diameter Range     | 0 - 0    |
| Width - Pad                  | 2 in     |

## Electrical Ratings

|                     |          |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

## Conductor Related

|                                 |                     |
|---------------------------------|---------------------|
| Clamping Range                  | 0 - 0               |
| Conductor Compatibility         | ACSR-Swift-636-36/1 |
| Conductor Diameter (Main) Range | 0 - 0               |

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)