

## Compression Deadend

By FARGO

Catalog # [A091021](#)

Compression Deadend, Uni-Grip, Single Tongue, Adjustable Clevis, for ACSR 477 kcmil 26/7, With Terminal



### Features

- For use with ACSR code name Hawk
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- Jumper Terminal & Mounting Hardware included

### General

Compression Method	Uni-Grip (single die system)
Die Size	10CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Single Tongue, Adjustable Clevis
Type	Compression
UPC	096359277170

### Dimensions

Bolt Diameter	0.750 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	0.858 in
Length Before Compression	21 in
Maximum Adjustment	2.8 in
Messenger Diameter Range	0 - 0
Weight	6.370 lb
Width - Pad	2 in

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Hawk-477-26/7
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)