

Compression Deadend

By FARGO
Catalog # [A091350NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Adjustable Clevis, for ACSR 954 kcmil 45/7, Without Terminal



Features

- For use with ACSR code name Rail
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	13CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Single Tongue, Adjustable Clevis
Terminal Option	No
Type	Compression
UPC	096359277200

Dimensions

Bolt Diameter	1.000 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	1.165 in
Length Before Compression	27 in
Maximum Adjustment	3.5 in
Messenger Diameter Range	0 - 0
Weight	1.840 lb
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Rail-954-45/7
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)