

## Compression Deadend

By FARGO  
Catalog # [A091974NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Adjustable Clevis, for ACSR 2312 kcmil 76/19, Without Terminal



### Features

- For use with ACSR code name Thrasher
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

### General

Compression Method	Uni-Grip (single die system)
Die Size	19CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	4
Press Minimum	100 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Single Tongue, Adjustable Clevis
Terminal Option	No
Type	Adjustable Clevis

### Dimensions

Bolt Diameter	1.100 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	1.802 in
Length Before Compression	36.4 in
Maximum Adjustment	4.4 in
Messenger Diameter Range	0 - 0
Width - Pad	4 in

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	ACSR-Thrasher-2312-76/19
Conductor Diameter (Main) Range	0 - 0

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)