

Compression Deadend

By FARGO
Catalog # [A100708](#)

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for ACSR 266.8 kcmil 18/1, With Terminals



*Representative Image

General

Compression Method	Uni-Grip (single die system)
Die Size	07CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Type	Compression

Dimensions

Bolt Diameter	0.620 in
Diameter - Clamping Hardware	0 in
Diameter - Outside	0.609 in
Length Before Compression	18.5 in
Maximum Adjustment	2.9 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Waxwing-266.8-18/1
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)