

Compression Splice Uni-Grip® (One Die) Full Tension

By FARGO
Catalog # A151346



"Compression Splice, Uni-Grip, Full Tension, for ACSR 1590.0 kcmil 45/7"

*Representative Image

Features

- "For use with ACSR Mallard
- Full tension Splice assembly
- Splices are prefilled with Inhibitor
- For Extra Length Repair Splice Add "XL" suffix and repair cutoff length in Inches e.g. A151346XL24
- Splices are EHV rated where conductor dia. is 1" or larger"

General

Compression Method	Uni-Grip (single die system)
Die Size	13CD
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	60 to
UPC	096359502173

Dimensions

Diameter - Outside	1.14 in
Length Before Compression	23.4 in
Messenger Diameter Range	0 - 0
Weight	5.096 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Mallard-795-30/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)