

Compression Splice Uni-Grip®(One Die) Full Tension

By FARGO
Catalog # [A151768](#)



"Compression Terminal, Uni-Grip, Jumper Terminal, 15 degree,
For ACSR, AAC, AAAC, ACAR. Standard Aluminum Range:
0.595"-0.679", Compact/TW range: 0.547"-0.611"

*Representative Image

Features

- "For use with ACSR Falcon
- Full tension Splice assembly
- Splices are prefilled with Inhibitor
- For Extra Length Repair Splice Add "XL" suffix and repair cutoff length in Inches e.g. A151768XL24
- Splices are EHV rated where conductor dia. is 1" or larger"

General

Compression Method	Uni-Grip (single die system)
Die Size	17CD
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	60 to
UPC	096359502180

Dimensions

Diameter - Outside	1.545 in
Length Before Compression	30.6 in
Messenger Diameter Range	0 - 0
Weight	11.035 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Falcon-1590-54/19
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)