

Compression Splice Uni-Grip®(One Die) Full Tension

By FARGO
Catalog # [A151973](#)



"Compression Terminal, Uni-Grip, Jumper Terminal, 15 degree, For ACSR, AAC, AAAC, ACAR. Standard Aluminum Range: 0.950"-1.045", Compact/TW range: 0.880"-0.930"

*Representative Image

Features

- "For use with ACSR Kiwi
- Full tension Splice assembly
- Splices are prefilled with Inhibitor
- For Extra Length Repair Splice Add "XL" suffix and repair cutoff length in Inches e.g. A151973XL24
- Splices are EHV rated where conductor dia. is 1" or larger"

General

Compression Method	Uni-Grip (single die system)
Die Size	19CD
Material	Aluminum Alloy
Press Minimum	100 to
UPC	096359278023

Dimensions

Diameter - Outside	1.735 in
Length Before Compression	34.2 in
Messenger Diameter Range	0 - 0

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Kiwi-2167-72/7
Conductor Diameter (Main) Range	0 - 0
Conductor Type	ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)