

Compression Splice Uni-Grip® (One Die) Full Tension

By FARGO
Catalog # [AB152020](#)



"Compression Splice, Uni-Grip, Full Tension, for ACSR 477.0 kcmil 30/7"

*Representative Image

Features

- "Limited tension Splice
- Splices are prefilled with Inhibitor
- For Extra Length Repair Splice Add "XL" suffix and repair cutoff length in Inches e.g. AB152020XL24
- Splices are EHV rated where conductor dia. is 1" or larger"

General

Compression Method	Uni-Grip (single die system)
Die Size	20CD
Material	Aluminum Alloy
Press Minimum	100 to
UPC	096359616542

Dimensions

Length Before Compression	36 in
Messenger Diameter Range	0 - 0
Weight	11.760 lb

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACAR-2493-72/19;ACAR-2493-54/37
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.9 in
Conductor Diameter - Minimum	1.806 in
Conductor Diameter Range	1.806 - 1.9

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)