

Formed Wire False Deadend for Bezinal® Guy Strand 5/16"

By FARGO
Catalog # [BFDE9106](#)

Formed Wire False Deadend for 5/16" Bezinal® Guy Strand



Features

- Allows strand to continue beyond the deadend pole
- For Bezinal® Guy Strand
- Bezinal® (B-coat) wire construction
- 11,200lb (49.8KN) maximum RBS

Application

False Deadend for Bezinal® Guy Strand

General

Color Code	Black
Material	Zinc-Aluminum Coated Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359710967

Dimensions

Length	39 in
Nominal Guy Wire Size	5/16" Bezinal®
Weight	0.955 lb

Conductor Related

Conductor Diameter - Maximum	0.336 in
Conductor Diameter - Minimum	0.292 in
Conductor Diameter Range	0.292 - 0.336
Conductor Type	Bezinal®
Guy Wire Type	Bezinal®

Logistics

Carton Quantity	25
Pallet Quantity	1400

Product Assets

[Literature - Formed Wire False Deadend \(SF05121E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - FWFDE/BFDE - Formed Wire False Deadends](#)

Related Products

[BFDE9104 - Formed Wire False Deadend for Bezinal® Guy Strand 1/4"](#)
[BFDE9107 - Formed Wire False Deadend for Bezinal® Guy Strand 3/8"](#)