

Formed Wire False Deadend for
Bezinal® Guy Strand 7/16"

By FARGO
Catalog # [BFDE9108](#)

Formed Wire False Deadend for 7/16" Bezinal® Guy Strand

Features

- Allows strand to continue beyond the deadend pole
- For Bezinal® Guy Strand
- Bezinal® (B-coat) wire construction
- 20,800lb (92.5KN) maximum RBS

Application

False Deadend for Bezinal® Guy Strand

General

Catalog Number	BFDE9108
Color Code	Green
Material	Zinc-Aluminum Coated Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359710981

Dimensions

Length	48 in
--------	-------



Nominal Guy Wire Size	7/16" Bezinal®
Weight	2 lb

Conductor Related

Conductor Diameter - Maximum	0.474 in
Conductor Diameter - Minimum	0.395 in
Conductor Diameter Range	0.395 - 0.474
Conductor Type	Bezinal®
Guy Wire Type	Bezinal®

Logistics

Carton Quantity	20
Pallet Quantity	560

Product Assets

- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Literature - Formed Wire Flas Deadend](#)
- [Sales Drawings - FWFDE/BFDE - Formed Wire False Deadends](#)
- [Specifications - BFDE9108](#)