

Compression Deadend

By FARGO
Catalog # [C020707NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Horizontal Eye, for AAC, Dia. Range 0.595 - 0.68, Without Terminals



*Representative Image

Features

- For use with AAC code names: Peony, Tulip, Daffodil
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	07CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Terminal Option	No
Type	Compression
UPC	096359623885

Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	10.1 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	AAC-Daffodil-350-19
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.68 in
Conductor Diameter - Minimum	0.595 in
Conductor Diameter Range	0.595 - 0.68

Logistics

Pallet Quantity	240
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)