

Compression Deadend

By FARGO
Catalog # [C021515](#)

Compression Deadend, Uni-Grip, Double Tongue, Vertical Eye, for AAC, Dia. Range 1.331 - 1.425, With Terminals



*Representative Image

Features

- For use with AAC code names: Columbine, Carnation, Gladiolus
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- Jumper Terminal & Mounting Hardware included

General

Compression Method	Uni-Grip (single die system)
Die Size	15CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Type	Compression

Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	17 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.425 in
Conductor Diameter - Minimum	1.331 in
Conductor Diameter Range	1.331 - 1.425

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)