

## Compression Deadend

By FARGO  
Catalog # [C021616NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Vertical Eye, for AAC, Dia. Range 1.426 - 1.52, Without Terminals



\*Representative Image

### Features

- For use with AAC code names: Coreopsis, Dogwood
- Full tension Deadend assembly
- Steel eye factory compressed in Vertical orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

### General

Compression Method	Uni-Grip (single die system)
Die Size	16CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Vertical Eye
Terminal Option	No
Type	Compression
UPC	096359372936

### Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	18.7 in
Messenger Diameter Range	0 - 0
Weight	9.610 lb
Width - Pad	3 in

### Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

### Conductor Related

Clamping Range	0- 0
Conductor Compatibility	AAC-Coreopsis-1590-61
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.52 in
Conductor Diameter - Minimum	1.426 in
Conductor Diameter Range	1.426 - 1.52

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)