

Compression Deadend

By FARGO
Catalog # [C030808NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Horizontal Eye, for AAC, Dia. Range 0.681 - 0.765, Without Terminals



Features

- For use with AAC code names: Canna, Four-O'Clock
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	08CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Terminal Option	No
Type	Compression

Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	10.7 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	AAC-Canna-397.5-19
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.765 in
Conductor Diameter - Minimum	0.681 in
Conductor Diameter Range	0.681 - 0.765

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)