

Compression Deadend

By FARGO
Catalog # [C031414NT](#)

Compression Deadend, Uni-Grip, Single Tongue, Horizontal Eye, for AAC, Dia. Range 1.236 - 1.33, Without Terminals



Features

- For use with AAC code names: Hawthorn, Narcissus
- Full tension Deadend assembly
- Steel eye factory compressed in Horizontal orientation
- Prefilled with joint compound
- Uni-Grip Deadends & Jumper Terminals for conductors 1" dia or larger are EHV rated
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	14CD
EU RoHS Indicator	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Eye
Style	Uni-Grip, Single Tongue, Horizontal Eye
Terminal Option	No
Type	Compression
UPC	096359293514

Dimensions

Diameter - Clamping Hardware	0 in
Length Before Compression	16.4 in
Messenger Diameter Range	0 - 0
Weight	6.200 lb
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	1.33 in
Conductor Diameter - Minimum	1.236 in
Conductor Diameter Range	1.236 - 1.33

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)