

Compression Deadend

By FARGO
Catalog # [C100909NT](#)

Compression Deadend, Uni-Grip, Double Tongue, Adjustable Clevis, for AAC, Dia. Range 0.766 - 0.855, Without Terminals



*Representative Image

Features

- For use with AAC code names: Goldentuft, Yarrow, Cosmos, Syringa, Zinnia, Hyacinth, Ganzania
- Full tension Deadend assembly
- Steel Adjustable Clevis threaded stub factory compressed in deadend
- Prefilled with joint compound
- "NT" suffix eliminates Jumper Terminal & Mounting Hardware

General

Compression Method	Uni-Grip (single die system)
Die Size	09CD
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Clevis	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pin (Cotter)	#304 Stainless Steel
Number of Bolt Holes	2
Press Minimum	12 to
Product Category	Adjustable Clevis
Style	Uni-Grip, Double Tongue, Adjustable Clevis
Terminal Option	No
Type	Compression

Dimensions

Bolt Diameter	0.620 in
Diameter - Clamping Hardware	0 in
Length Before Compression	17.5 in
Maximum Adjustment	2.9 in
Messenger Diameter Range	0 - 0
Width - Pad	2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0 - 0
Conductor Compatibility	AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.855 in
Conductor Diameter - Minimum	0.766 in
Conductor Diameter Range	0.766 - 0.855

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

