

Compression Splice Uni-Grip®(One Die) Full Tension

By FARGO
Catalog # C150909



Uni-grip one die full tension splice for AAC conductors. Made with an aluminum body prefilled with inhibitor and plugged barrel ends.

Features

- Full tension splice assembly
- For use with AAC conductors: Goldentuft, Yarrow, Cosmos, Syringa, Zinnia, Hyacinth, Ganzania, Cable range: 450-550kcmil
- Die size: 09CD
- Minimum press size: 12 tons
- Splices are prefilled with Inhibitor
- Splices are EHV rated where conductor dia. is 1" or larger

General

Catalog Number	C150909
Compression Method	Uni-Grip (single die system)
Die Size	09CD
EU RoHS Indicator	No
Material	Aluminum Alloy
Press Minimum	12 to
Tension Range	0 lb
UPC	096359495444

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole	0 in
Spacing	
Length Before Compression	10.8 in
Messenger Diameter Range	0 - 0
Weight	0.921 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0.855 in
Conductor Diameter - Minimum	0.766 in
Conductor Diameter Range	0.766 - 0.855
Conductor Type	AAC
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
UL Listed	No

Logistics

Pallet Quantity	1080
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - C150909](#)