

Formed Wire Distribution Grip Deadend #2

By FARGO
Catalog # [DGFW4542](#)



Formed Wire Distribution Grip Deadend for #2 ACSR, AAC, AAAC, Compacted ACSR and AWAC® (#2 6/1, #3 5/2)

*Representative Image

Features

- For deadending bare or plastic jacketed conductor on primaries, secondaries, and substation feeder applications
- For use on ACSR, AAC, AAAC, Compacted ACSR and AWAC®
- Aluminum clad steel construction
- DGFW deadends will hold a minimum of 60% of the cable (RBS) rated breaking strength.

Application

Deadend for Distribution Feeder

General

Color Code	Red
Material	Aluminum Clad Steel
Product Category	Overhead
Type	Formed Wire
UPC	096359451655

Dimensions

Dimensions	24.000 in x 0.487 in x 3.224 in
Height	3.224 in
Length	24.000 in
Weight	0.306 lb
Width	0.487 in

Conductor Related

Conductor Diameter - Maximum	0.325
Conductor Diameter - Minimum	0.29
Conductor Diameter Range	0.29 - 0.325
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR and AWAC®

Logistics

Carton Quantity	100
Pallet Quantity	2400

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - DGFW Formed Wire Distribution Grip](#)

Related Products

[DGFW4541 - Formed Wire Distribution Grip Deadend #4](#)
[DGFW4543 - Formed Wire Distribution Grip Deadend #1](#)