

Formed Wire Distribution Grip Deadend #1

By FARGO
Catalog # [DGFW4543](#)



Formed Wire Distribution Grip Deadend for #1 ACSR, AAC, AAAC, Compacted ACSR and AWAC® (#1 6/1, #2 5/2)

*Representative Image

Features

- For deadending bare or plastic jacketed conductor on primaries, secondaries, and substation feeder applications
- For use on ACSR, AAC, AAAC, Compacted ACSR and AWAC®
- Aluminum clad steel construction
- DGFW deadends will hold a minimum of 60% of the cable (RBS) rated breaking strength.

Application

Deadend for Distribution Feeder

General

Color Code	Green
Material	Aluminum Clad Steel
Product Category	Overhead
Type	Formed Wire
UPC	096359641544

Dimensions

Length	26 in
Weight	0.544 lb

Conductor Related

Conductor Diameter - Maximum	0.364
Conductor Diameter - Minimum	0.326
Conductor Diameter Range	0.326 - 0.364
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR and AWAC®

Logistics

Carton Quantity	50
Pallet Quantity	1400

Product Assets

[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - DGFW Formed Wire Distribution Grip](#)

Related Products

[DGFW4542 - Formed Wire Distribution Grip Deadend #2](#)
[DGFW4544 - Formed Wire Distribution Grip Deadend 1/0](#)