

HUBBELL

Power Systems

Formed Wire Deadend for Guy Strand 5/16"

By FARGO
Catalog # FWDE1106



Formed Wire Deadend for 5/16" Guy Strand

Features

For HSS, EHS, Common Siemens-Martin; Utilities and Bell System Strand grades; Zinc plated (B-coat) EHS steel construction; 11200lb (49.8KN) maximum RBS

General

Application	Deadend for Guy Strand
Color Code	Black
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359366072

Dimensions

Dimensions	31.000 in x 0.460 in x 3.045 in
Height	3.045 in
Length	31 in
Nominal Guy Wire Size	5/16" 7 Strand
Weight	0.82 lb
Width	0.46 in

Conductor Related

Conductor Diameter - Maximum	0.336 in
Conductor Diameter - Minimum	0.292 in
Conductor Diameter Range	0.292 - 0.336
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	50
Pallet Quantity	1400

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Literature - FORMED WIRE DEADENDS](#)
- [Sales Drawings - FWDE Formed Wire Deadend](#)
- [Video - HPS Formed Wire Dead End Install](#)



A Hubbell brand