

Formed Wire Deadend for Guy
Strand 5/16"

By FARGO
Catalog # [FWDE1106TE](#)



Formed Wire Deadend for 5/16" Guy Strand, Tapered Ends

Features

- For HSS, EHS, Common Siemens-Martin
- Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- Tapered Ends
- 11200lb (49.8KN) maximum RBS

Application

Deadend for Guy Strand

General

Catalog Number	FWDE1106TE
Color Code	Black
EU RoHS Indicator	No
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359375586

Dimensions

Length	31 in
Nominal Guy Wire Size	5/16" 7 Strand

Weight	0.79 lb
--------	---------

Conductor Related

Conductor Diameter - Maximum	0.336
Conductor Diameter - Minimum	0.292
Conductor Diameter Range	0.292 - 0.336
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	50
Pallet Quantity	1400

Product Assets

- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - FWDE_TE_Sales Drawing](#)
- [Specifications - FWDE1106TE](#)
- [Video - HPS Formed Wire Dead End Install](#)