

Formed Wire Deadend for Guy
Strand 7/16"

By FARGO
Catalog # FWDE1108



Formed Wire Deadend for 7/16" Guy Strand

Features

- For HSS, EHS, Common Siemens-Martin
- Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 20800lb (92.5KN) maximum RBS

Application

Deadend for Guy Strand

General

Catalog Number	FWDE1108
Color Code	Green
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359366096

Dimensions

Dimensions	38.000 in x 0.598 in x 3.446 in
Height	3.446 in
Length	38 in
Nominal Guy Wire Size	7/16" 7 Strand
Weight	1.44 lb
Width	0.598 in

Conductor Related

Conductor Diameter - Maximum	0.474 in
Conductor Diameter - Minimum	0.395 in
Conductor Diameter Range	0.395 - 0.474
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	25
Pallet Quantity	700

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Literature - FORMED WIRE DEADENDS](#)
- [Sales Drawings - FWDE Formed Wire Deadend](#)
- [Specifications - FWDE1108](#)
- [Video - HPS Formed Wire Dead End Install](#)