

Formed Wire Deadend for Guy  
Strand 1/2"

By FARGO  
Catalog # FWDE2115TE



Formed Wire Deadend for 1/2" Guy Strand, Tapered Ends

Features

- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- Tapered Ends
- 26,900lb (119.7KN) maximum RBS

Application

Deadend for Guy Strand

General

Catalog Number	FWDE2115TE
Color Code	Blue
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359571384

Dimensions

Length	49 in
--------	-------

Nominal Guy Wire Size	1/2" 7 Strand
Weight	3 lb

Conductor Related

Conductor Diameter - Maximum	0.515
Conductor Diameter - Minimum	0.475
Conductor Diameter Range	0.475 - 0.515
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	20
Pallet Quantity	360

Product Assets

- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - FWDE\\_TE\\_Sales Drawing](#)
- [Specifications - FWDE2115TE](#)
- [Video - HPS Formed Wire Dead End Install](#)