

Formed Wire False Deadend for Guy Strand 1/4"

By FARGO
Catalog # [FWFDE1104](#)

Formed Wire False Deadend for 1/4" Guy Strand



Features

- Allows strand to continue beyond the deadend pole
- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 6,650lb (29.6KN) maximum RBS

Application

False Deadend for Guy Strand

General

Color Code	Yellow
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359710295

Dimensions

Length	36 in
Nominal Guy Wire Size	1/4" 7 Strand
Weight	0.635 lb

Conductor Related

Conductor Diameter - Maximum	0.259
Conductor Diameter - Minimum	0.231
Conductor Diameter Range	0.231 - 0.259
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	25
Pallet Quantity	1050

Product Assets

- [Literature - Formed Wire Flas Deadend \(SF05121E\)](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - FWFDE/BFDE - Formed Wire False Deadends](#)
- [Video - HPS Formed Wire Dead End Install \(VI05011E\)](#)