

## Formed Wire False Deadend for Guy Strand 3/8"

By FARGO  
Catalog # [FWFDE1107](#)

Formed Wire False Deadend for 3/8" Guy Strand



### Features

- Allows strand to continue beyond the deadend pole
- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 15,400lb (68.5KN) maximum RBS

### Application

False Deadend for Guy Strand

### General

Color Code	Orange
Material	Galvanized Steel
Product Category	Guy Wire
Type	Formed Wire
UPC	096359710318

### Dimensions

Length	42 in
Nominal Guy Wire Size	3/8" 7 Strand
Weight	1.185 lb

### Conductor Related

Conductor Diameter - Maximum	0.394
Conductor Diameter - Minimum	0.337
Conductor Diameter Range	0.337 - 0.394
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

### Logistics

Carton Quantity	25
Pallet Quantity	1400

### Product Assets

- [Literature - Formed Wire Flas Deadend \(SF05121E\)](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - FWFDE/BFDE - Formed Wire False Deadends](#)
- [Video - HPS Formed Wire Dead End Install \(VI05011E\)](#)