

Formed Wire Line Splice for Guy Strand 5/16"

By FARGO
Catalog # [FWLS2106](#)



Formed Wire Line Splice for 5/16" Guy Strand

*Representative Image

Features

- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 11,200lb (49.8kN) maximum RBS

Application

Line Splice for Guy Strand

General

Color Code	Black
Material	Galvanized Steel
Product Category	Splices
Type	Formed Wire
UPC	096359576518

Dimensions

Dimensions	42.000 in x 0.460 in x 0.460 in
Height	0.460 in
Length	42.000 in
Nominal Guy Wire Size	5/16" 7 Strand
Weight	0.920 lb
Width	0.460 in

Conductor Related

Conductor Diameter - Maximum	0.336 in
Conductor Diameter - Minimum	0.292 in
Conductor Diameter Range	0.292 - 0.336
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	50
Pallet Quantity	750

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - FWLS Formed Wire Guy Splice](#)