

Formed Wire Line Splice for Guy Strand 7/16"

By FARGO
Catalog # [FWLS2108](#)



Formed Wire Line Splice for 7/16" Guy Strand

*Representative Image

Features

- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 20,800lb (92.5kN) maximum RBS

Application

Line Splice for Guy Strand

General

Color Code	Green
Material	Galvanized Steel
Product Category	Splices
Type	Formed Wire
UPC	096359576532

Dimensions

Length	56 in
Nominal Guy Wire Size	7/16" 7 Strand
Weight	2.000 lb

Conductor Related

Conductor Diameter - Maximum	0.474 in
Conductor Diameter - Minimum	0.395 in
Conductor Diameter Range	0.395 - 0.474
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Sales Drawings - FWLS Formed Wire Guy Splice](#)