

Formed Wire Line Splice for Guy Strand 1/2"

By FARGO
Catalog # [FWLS2109](#)



Formed Wire Line Splice for 1/2" Guy Strand

*Representative Image

Features

- For HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand grades
- Zinc plated (B-coat) EHS steel construction
- 26,900lb (119.7kN) maximum RBS

Application

Line Splice for Guy Strand

General

Color Code	Blue
Material	Galvanized Steel
Product Category	Splices
Type	Formed Wire
UPC	096359576549

Dimensions

Length	63 in
Nominal Guy Wire Size	1/2" 7 Strand
Weight	4.900 lb

Conductor Related

Conductor Diameter - Maximum	0.515 in
Conductor Diameter - Minimum	0.475 in
Conductor Diameter Range	0.475 - 0.515
Conductor Type	Galvanized Steel
Guy Wire Type	Galvanized Steel

Logistics

Carton Quantity	10
Pallet Quantity	420

Product Assets

[Sales Drawings - FWLS Formed Wire Guy Splice](#)