

Stirrup Clamp

By FARGO
Catalog # [GA104SL](#)

Overhead Stirrup, Bolted, Stirrup, Vise Type, Aluminum,
AAC|AAAC|ACSR, Range 0.232 - 0.563 in



*Representative Image

Features

Vise type action develops vibration proof connection on conductor.

General

Catalog Number	GA104SL
Hot Stick Eyes	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum
Material - Eyestem	Forged Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Spring (on Eyestem)	Stainless Steel
Material - Stirrup	Copper
Material - Washer	Stainless Steel
Number of Eyebolts	1
Plating	No
Type	Stirrups
UPC	096359304203

Dimensions

Copper Loop Size	0.258 in
Diameter - Bolt	0.4375 in
Diameter - Stirrup Nominal Wire	#2 Solid
Dimensions	4.500 in x 2.500 in x 5.750 in
Height	5.75 in
Length	4.5 in
Weight	0.84 lb
Width	2.5 in
Width - Main Contact	2.5 in

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-
-------------------------	---

Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18

Conductor Diameter - Maximum	0.563
Conductor Diameter - Minimum	0.232
Conductor Diameter Range	0.232 - 0.563
Conductor Type	Aluminum

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Packaging Type	Bag
Pallet Quantity	800

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Specifications - GA104SL](#)
- [Video - Hubbell Power Systems In Depth: Stirrup Clamps](#)
- [Video - Hubbell Power Systems Hotline Tap Clamps and Stirrup Clamps](#)