


Connector, Vise-Type

By FARGO
Catalog # [GA9041GLO](#)



Single Bolt Aluminum Vise-Type Connector.

*Representative Image

Features

- Recommended for aluminum or aluminum to copper distribution, service or tap connections
- Sealant is recommended on all connectors
- Optional snap-on cover available

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	300 lb/ft
EU RoHS Indicator	No
Grommets	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Spacer	Aluminum
Plating	No
Product Category	Clamps
Style	Single Bolt
UPC	096359304852

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Diameter - Bolt Head	0.75 in
Dimensions	1.500 in x 3.375 in x 3.125 in
Height	3.125 in
Length	1.500 in
Weight	0.570 lb
Width	3.375 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.563 in
Conductor Diameter (Main) - Minimum	0.289 in
Conductor Diameter (Main) Range	0.289 - 0.563
Conductor Diameter (Tap) - Maximum	0.447 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Type	Aluminum/Copper

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	4200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - CC-20308](#)

Related Products

[GA9041GLSS - Connector, Vise-Type](#)
[GA9041GAAO - Connector, Vise-Type](#)