

HUBBELL Power Systems

Connector, Vise-Type

By FARGO

Catalog # [GA9954GL](#)

Single Bolt Aluminum Vise-Type Connector



Oh No!
IMAGE COMING SOON

*Representative Image

Features

- Recommended for aluminum or aluminum to copper distribution, service or tap connections
- Sealant is recommended on all connectors
- Optional snap-on cover available

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	300 lb/ft
Catalog Number	GA9954GL
EU RoHS Indicator	No
Grommets	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Body	Aluminum Alloy
Material - Bolt	Aluminum Alloy
Material - Hardware	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Spacer	Aluminum
Plating	No
Product Category	Clamps
Style	Single Bolt
UPC	096359305248

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Diameter - Bolt Head	0.75 in
Dimensions	3.000 in x 3.000 in x 4.750 in
Height	4.75 in
Length	3 in
Length - Nut Flat-To-Flat	0.75 in
Weight	1.215 lb
Width	3 in

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Brahma-203.2-16/19;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18;ACAR-853.7-30/7
Conductor Diameter (Main) - Maximum	1.126 in
Conductor Diameter (Main) - Minimum	1.026 in
Conductor Diameter (Main) Range	1.026 - 1.126
Conductor Diameter (Tap) - Maximum	0.666 in
Conductor Diameter (Tap) - Minimum	0.368 in
Conductor Diameter - Maximum	1.126 in
Conductor Diameter - Minimum	1.026 in
Conductor Diameter Range	1.026 - 1.126
Conductor Type	Aluminum/Copper

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GA9954GL-SPEC-EN | REV 6/2024