

HUBBELL Power Systems

Connector, Vise-Type

By FARGO
Catalog # [GC166](#)

Grounding Vise-Type Connector



*Representative Image

Features

Side Opening Jaw facilitates easy installation.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Catalog Number	GC166
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307167

Dimensions

Bolt Diameter	0.25
Diameter - Bolt	0.25 in
Diameter - Bolt Head	0.31 in
Dimensions	1.000 in x 0.875 in x 1.500 in
Height	1.5 in
Length	1 in
Length - Nut Flat-To-Flat	0.38 in
Weight	0.42 lb
Width	0.875 in

Conductor Related

Conductor Diameter - Maximum	0.5
Conductor Diameter - Minimum	0.245
Conductor Diameter Range	0.245 - 0.5
Conductor Type	Messenger Wire

Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand