

Connector, Vise-Type

By FARGO
Catalog # [GC167](#)



Grounding Vise-Type Connector

*Representative Image

Features

Side Opening Jaw facilitates easy installation.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Catalog Number	GC167
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307204

Dimensions

Bolt Diameter	0.31
Diameter - Bolt	0.31 in
Diameter - Bolt Head	0.56 in
Dimensions	1.000 in x 1.250 in x 1.625 in
Height	1.625 in
Length	1 in

Length - Nut Flat-To-Flat	0.56 in
Weight	0.206 lb
Width	1.25 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.312 in
Conductor Diameter (Main) - Minimum	0.146 in
Conductor Diameter (Main) Range	0.146 - 0.312
Conductor Diameter (Tap) - Maximum	0.312 in
Conductor Diameter (Tap) - Minimum	0.146 in
Conductor Diameter - Maximum	0.312
Conductor Diameter - Minimum	0.146
Conductor Diameter Range	0.146 - 0.312
Conductor Type	Insulated Conductor

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Product Assets

[Catalogs - Distribution Connectors](#)
[Specifications - GC167](#)