


HUBBELL

Power Systems

Grounding Clamp, #4 Sol. - 1/0 Str.

By FARGO
Catalog # [GC5020](#)

Grounding Clamp, Copper Cable to Cable, Vice Type.



*Representative Image

Features

- For copper connections
- One piece design for easier, faster installation
- Vice design achieves high connector pressure with low wrench force

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	180 in-lbs
Catalog Number	GC5020
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307518

Dimensions

Bolt Diameter	0.313 in
	0.313 in
Diameter - Bolt	0.3125 in
Diameter - Bolt Head	0.375 in
Dimensions	1.125 in x 0.750 in x 1.875 in
Height	1.875 in
Length	1.125 in
Weight	0.225 lb
Width	0.75 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.39 in
Conductor Diameter (Main) - Minimum	0.204 in
Conductor Diameter (Tap) - Maximum	0.39 in
Conductor Diameter (Tap) - Minimum	0.204 in
Conductor Type	Copper

Logistics

Pallet Quantity	6000
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - CC-25775](#)
[Video - Hubbell Power Systems Vice Type Clamp](#)
[Video - Hubbell Power Systems Bolted Parallel Groove, Vise Type, and U Bolt Clamps](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GC5020-SPEC-EN | REV 6/2024