

Grounding Clamp, #3 Sol. - 2/0 Str.

By FARGO
Catalog # [GC5020S](#)



Grounding Clamp, Copper Cable to Cable, Vice Type.

*Representative Image

Features

- For copper connections
- One piece design for easier, faster installation
- Vise design achieves high connector pressure with low wrench force

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Catalog Number	GC5020S
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307549

Dimensions

Bolt Diameter	0.375 in
Diameter - Bolt	0.375 in
Diameter - Bolt Head	0.375 in
Dimensions	1.250 in x 0.875 in x 2.000 in
Height	2 in
Length	1.25 in

Weight	0.384 lb
Width	0.875 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.438 in
Conductor Diameter (Main) - Minimum	0.229 in
Conductor Diameter (Tap) - Maximum	0.438 in
Conductor Diameter (Tap) - Minimum	0.229 in
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	3500
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - CC-25775](#)
- [Specifications - GC5020S](#)
- [Video - Hubbell Powet Systems Vice Type Clamp](#)
- [Video - Hubbell Power Systems Bolted Parallel Groove, Vise Type, and U Bolt Clamps](#)