

# HUBBELL

## Power Systems

### Grounding Clamp, #1 Sol. - 4/0 Str.

By FARGO  
Catalog # [GC5040](#)

Grounding Clamp, Copper Cable to Cable, Vice Type.



\*Representative Image

#### Features

- For copper connections
- One piece design for easier, faster installation
- Vise design achieves high connector pressure with low wrench force

#### General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Catalog Number	GC5040
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307594

#### Dimensions

Bolt Diameter	0.375 in
	0.375 in
Diameter - Bolt	0.375 in
Diameter - Bolt Head	0.375 in
Dimensions	1.375 in x 1.000 in x 2.125 in
Height	2.125 in
Length	1.375 in
Weight	0.48 lb
Width	1 in

#### Conductor Related

Conductor Diameter (Main) - Maximum	0.552 in
Conductor Diameter (Main) - Minimum	0.289 in
Conductor Diameter (Tap) - Maximum	0.552 in
Conductor Diameter (Tap) - Minimum	0.289 in
Conductor Type	Copper

#### Logistics

Pallet Quantity	4800
-----------------	------

#### Product Assets

[Catalogs - Distribution Connectors](#)  
[Sales Drawings - CC-25775](#)  
[Video - Hubbell Power Systems Vice Type Clamp](#)  
[Video - Hubbell Power Systems Bolted Parallel Groove, Vise Type, and U Bolt Clamps](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
FG-GC5040-SPEC-EN | REV 6/2024