

Connector, Vise-Type

By FARGO
Catalog # [GC8020GL](#)



Single Bolt Bronze Vise-Type Connector with Spacer

*Representative Image

Features

Will accept two maximum sized conductors.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Catalog Number	GC8020GL
Grommets	Yes
Inhibitor Loaded	Yes
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307761

Dimensions

Bolt Diameter	0.313 in
Diameter - Bolt	0.3125 in
Diameter - Bolt Head	0.56 in
Dimensions	1.125 in x 1.375 in x 1.750 in
Height	1.75 in
Length	1.125 in

Length - Nut Flat-To-Flat	0.56 in
Weight	0.32 lb
Width	1.375 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.41 in
Conductor Diameter (Main) - Minimum	0.128 in
Conductor Diameter (Main) Range	0.128 - 0.41
Conductor Diameter (Tap) - Maximum	0.41 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	6000
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - CC-25843](#)
- [Specifications - GC8020GL](#)