

Copper Automatic Dead End, #3 SOL, #4 STR Copper, 6A CW, Semi-Flex Bail.

By FARGO
Catalog # [GD113R](#)



Copper Automatic Dead End, #3 SOL, #4 STR Copper, 6A CW, Conductor Range .22 - .23" (5.7- 5.9 mm), Semi-Flex Bail.

*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Semi-Flex Bail
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359307983

Dimensions

Length	6.880 in
Weight	0.200 lb
Width	0.780 in

Conductor Related

Conductor Diameter - Maximum	0.23
Conductor Diameter - Minimum	0.22
Conductor Diameter Range	0.22 - 0.23

Logistics

Pallet Quantity	7200
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-24780](#)