

Copper Automatic Dead End, #1 SOL, #2 STR Copper, 4A CW, Semi-Flex Bail.

By FARGO  
Catalog # [GD115R](#)

Copper Automatic Dead End, #1 SOL, #2 STR Copper, 4A CW, Conductor Range .28 - .29" (7.2 - 7.4 mm) , Semi-Flex Bail.

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Semi-Flex Bail
Catalog Number	GD115R
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359308096

Dimensions



\*Representative Image

Length	8.88 in
Weight	0.44 lb
Width	0.935 in

Conductor Related

Conductor Diameter - Maximum	0.29
Conductor Diameter - Minimum	0.28
Conductor Diameter Range	0.28 - 0.29

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	2100
-----------------	------

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - CC-24780](#)
- [Specifications - GD115R](#)