

Copper Automatic Dead End, 3/0 SOL, 2/0 STR Copper, Flex Bail.

By FARGO
Catalog # [GD118](#)

Copper Automatic Dead End, 3/0 SOL, 2/0 STR Copper,
Conductor Range .40 - .41" (10.2 - 10.5 mm), Flex Bail.



*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Flex Bail
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Flex Bail
Type	Automatic
UPC	096359308218

Dimensions

Weight 0.630 lb

Conductor Related

Conductor Diameter - Maximum 0.41
 Conductor Diameter - Minimum 0.4
 Conductor Diameter Range 0.4 - 0.41

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-24780](#)