

Copper Automatic Dead End, 4/0 STR Copper, Semi-Flex Bail.

By FARGO
Catalog # [GD120R](#)

Copper Automatic Dead End, 4/0 STR Copper, Conductor Range .52 - .53" (13.2 - 13.4 mm), Semi-Flex Bail.



*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

| | |
|-------------------|----------------------|
| Bail Option | Semi-Flex Bail |
| EU RoHS Indicator | Contact Manufacturer |
| Material | Copper; Steel |
| Material - Bail | Stainless Steel |
| Material - Shell | Copper Alloy |
| Product Category | Semi-Flex Bail |
| Type | Automatic |
| UPC | 096359308409 |

Dimensions

Weight 1.470 lb

Conductor Related

Conductor Diameter - Maximum 0.53
 Conductor Diameter - Minimum 0.52
 Conductor Diameter Range 0.52 - 0.53

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-24780](#)