


HUBBELL

Power Systems

Aluminum Automatic Dead End, 3/0 AAC, 3/0 AAAC, 3/0 ACSR Conductor, Semi-Flex Bail.

By FARGO
Catalog # [GD468](#)

Aluminum Automatic Dead End, 3/0 AAC, 3/0 AAAC, 3/0 ACSR Conductor, Diameter range .450 - .530" (11.43 - 13.46 mm), Semi-Flex Bail.



*Representative Image

Features

- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- Galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)

General

Bail Option	Semi-Flex Bail
Catalog Number	GD468
Color Code	Black
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Bail	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Semi-Flex Bail
Type	Automatic
UPC	096359309246

Dimensions

Weight	1.08 lb
--------	---------

Conductor Related

Conductor Compatibility	ACSR-Pigeon-3/0-6/1;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Amherst-195.7-6/18
Conductor Diameter - Maximum	0.53
Conductor Diameter - Minimum	0.45
Conductor Diameter Range	0.45 - 0.53

Logistics

Pallet Quantity	840
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Literature - Deadends For Overhead Connections](#)
[Sales Drawings - GD-440A_Series_Overhead_Automatic_Deadend\(CC-25241\)](#)
[Sales Drawings - CC-25241](#)

