

# Copper Automatic Dead End, #1 SOL and #2 STR Copper, 4A CW Conductor, Clevis Bail.

By FARGO  
Catalog # [GD515](#)



Copper Automatic Dead End, #1 SOL and #2 STR Copper, 4A CW Conductor, Diameter range .28 - .29" (7.2 - 7.4 mm) , Clevis Bail.

\*Representative Image

## Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

## General

Bail Option	Clevis Bail
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Clevis Bail
Type	Automatic
UPC	096359309338

## Dimensions

Weight 1.060 lb

## Conductor Related

Conductor Diameter - Maximum 0.29  
 Conductor Diameter - Minimum 0.28  
 Conductor Diameter Range 0.28 - 0.29

## Logistics

Pallet Quantity 2100

## Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - CC-24780](#)