

Copper Automatic Dead End, 3/0 SOL and 2/0 STR Copper, Clevis Bail.

By FARGO
Catalog # [GD518](#)



Copper Automatic Dead End, 3/0 SOL and 2/0 STR Copper Conductor, Diameter range .40 - .41" (10.2 - 10.5 mm), Clevis Bail.

*Representative Image

Features

- Fastest method of deadending Copper and Copperweld® conductor
- Flared mouth of gripping unit permits easy conductor installation
- Four segment jaw is precision machined and automatically adjusts to the contour of the wire
- High strength alloy copper tube for gripping Copperweld® conductors

General

Bail Option	Clevis Bail
EU RoHS Indicator	Contact Manufacturer
Material	Copper; Steel
Material - Bail	Galvanized Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Shell	Copper Alloy
Product Category	Clevis Bail
Type	Automatic
UPC	096359309383

Dimensions

Weight 1.180 lb

Conductor Related

Conductor Diameter - Maximum 0.41
 Conductor Diameter - Minimum 0.4
 Conductor Diameter Range 0.4 - 0.41

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - CC-24780](#)