

HUBBELL
Power Systems

Deadend, Straight line, Swing Away,
Side Opening, #4 7 STR to 477 37
STR AL, #4 6/1 to 397.5 30/7 ACSR,
Fitting: NONE

By FARGO
Catalog # [GD963A](#)



*Representative Image

Deadend, Straight line, Swing Away, Side Opening, #4 7 STR to 477 37 STR AL, #4 6/1 to 397.5 30/7 ACSR, Conductor Range 0.25 - 0.81 in, Fitting: NONE

Features

- For distribution and light transmission construction.
- The pressure pad is easily lifted and swung clear of the cable groove permitting convenient top loading of the conductor without disassembly.
- The large pulling eye makes it convenient to connect and disconnect the “come-along” hook.

General

Catalog Number	GD963A
Fitting Type	NONE
Material	Aluminum
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Product Category	Straight Line
Strength Rating - Ultimate	10000 lb
Body	
Style	GD900
Type	Bolted
UPC	096359309727

Dimensions

Clevis Opening	0.75 in
Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Length	10 in
Weight	2 lb
Width	0.75 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Sparrow-2-6/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-
-------------------------	--

6/1;ACSR-Pigeon-3/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Brahma-203.2-16/19;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

Conductor Diameter - Maximum	0.81
Conductor Diameter - Minimum	0.25
Conductor Diameter Range	0.25 - 0.81

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	640
-----------------	-----

Product Assets

