

HUBBELL  
Power Systems

Deadend, Straight line, Swing Away,  
Side Opening, 4/0 7STR to 556.5 37  
STR AL, 3/0 6/1 to 556.5 18/1 ACSR,  
Fitting: NONE

By FARGO  
Catalog # [GD965A](#)



\*Representative Image

Deadend, Straight line, Swing Away, Side Opening, 4/0 7STR to 556.5 37 STR AL, 3/0 6/1 to 556.5 18/1 ACSR, Conductor Range 0.5 - 0.88 in, Fitting: NONE

Features

- For distribution and light transmission construction.
- The pressure pad is easily lifted and swung clear of the cable groove permitting convenient top loading of the conductor without disassembly.
- The large pulling eye makes it convenient to connect and disconnect the “come-along” hook.

General

|                            |                       |
|----------------------------|-----------------------|
| Catalog Number             | GD965A                |
| Fitting Type               | NONE                  |
| Material                   | Aluminum              |
| Material - Body            | 356 T6 Aluminum Alloy |
| Material - Hardware        | Galvanized Steel      |
| Material - Keeper          | 356 T6 Aluminum Alloy |
| Product Category           | Straight Line         |
| Strength Rating - Ultimate | 10000 lb              |
| Body                       |                       |
| Style                      | GD900                 |
| Type                       | Bolted                |
| UPC                        | 096359309741          |

Dimensions

|                 |           |
|-----------------|-----------|
| Clevis Opening  | 0.75 in   |
| Diameter - Bolt | 0.5 in    |
| Diameter - Pin  | 0.625 in  |
| Length          | 10.125 in |
| Weight          | 3.3 lb    |
| Width           | 0.75 in   |

Electrical Ratings

|                     |          |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

|                         |                                                                                               |
|-------------------------|-----------------------------------------------------------------------------------------------|
| Conductor Compatibility | ACSR-Turkey-6-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR- |
|-------------------------|-----------------------------------------------------------------------------------------------|

Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

|                              |            |
|------------------------------|------------|
| Conductor Diameter - Maximum | 0.88       |
| Conductor Diameter - Minimum | 0.5        |
| Conductor Diameter Range     | 0.5 - 0.88 |

Certifications And Compliance

|                          |                                                     |
|--------------------------|-----------------------------------------------------|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
|--------------------------|-----------------------------------------------------|

Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 320 |
|-----------------|-----|

Product Assets

[Catalogs - Distribution Connectors](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - CC-25270](#)



A Hubbell brand